



WDW101

IP20

Flush-mounted housing for WDI10x, flush with wall

Technical properties

Functions

Touch function	No
Function	with Push-to-open mechanism for comfortable mounting

Controls and indicators

Operation	depending on the software visualisation one and two surface operation, stepless configuration based on sliding and page scrolling by swiping are supported
-----------	--

Connectivity

Connection	RJ45 cable in scope of delivery
Connectors / jacks	with USB/Mini USB type A adapter cable ; with RJ45 connector kit from connector and patch cable

Dimensions

Cavity wall opening (W x H x D)	269 x 186 x 74 mm
---------------------------------	-------------------

Power

Total power loss under IN	0 W
Dissipated energy in cable	0 W

Screen

Display	no
---------	----

Materials

Material family	Metal
-----------------	-------

Installation, mounting

Installation mode	for flush-mounted and hollow-wall mounting ; for vertical and horizontal mounting
-------------------	---

Scope of delivery

Component	Microphone and loudspeaker with echo suppression
-----------	--

Equipment

Interface type	other
Text field	No
Lighting	Display illumination can be switched on automatically using brightness sensor
low noise	silent, long-lasting convection cooling without fan

Safety

REACH conform	Yes
---------------	-----

RoHS conform	Yes
Halogen free	Yes
Protection	with cleaning cover
Use conditions	
Storage/transport temperature	-20...60 °C
Relative humidity (without condensation)	10...90 %
Identification	
Composition	other
Main design line	KNX