



WDW101

IP20

## Flush-mounted housing for WDI10x, flush with wall

### Technical properties

#### Functions

Touch function	No
Function	with Push-to-open mechanism for comfortable mounting

#### Controls and indicators

Operation	depending on the software visualisation one and two surface operation, stepless configuration based on sliding and page scrolling by swiping are supported
-----------	--

#### Connectivity

Connection	RJ45 cable in scope of delivery
Connectors / jacks	with USB/Mini USB type A adapter cable ; with RJ45 connector kit from connector and patch cable

#### Dimensions

Cavity wall opening (W x H x D)	269 x 186 x 74 mm
---------------------------------	-------------------

#### Power

Total power loss under IN	0 W
Dissipated energy in cable	0 W

#### Screen

Display	no
---------	----

#### Materials

Material family	Metal
-----------------	-------

#### Installation, mounting

Installation mode	for flush-mounted and hollow-wall mounting ; for vertical and horizontal mounting
-------------------	---

#### Scope of delivery

Component	Microphone and loudspeaker with echo suppression
-----------	--

#### Equipment

Interface type	other
Text field	No
Lighting	Display illumination can be switched on automatically using brightness sensor
low noise	silent, long-lasting convection cooling without fan

#### Safety

REACH conform	Yes
---------------	-----

RoHS conform	Yes
Halogen free	Yes
Protection	with cleaning cover

---

**Use conditions**

Storage/transport temperature	-20...60 °C
Relative humidity (without condensation)	10...90 %

---

**Identification**

Composition	other
Main design line	KNX