



WE001



2 way switch single Essensya Pure

Technical properties

Architecture

| | |
|----------------------|----------------|
| Type of control unit | single rocker |
| Number of keys | 1 |
| Fixing mode | flush-mounting |

Controls and indicators

| | |
|----------------|----|
| Indicator lamp | no |
| Push-buttons | No |

Main electrical features

| | |
|-----------|----------|
| Frequency | 50/60 Hz |
|-----------|----------|

Electric current

| | |
|---------------|-------|
| Rated current | 10 AX |
|---------------|-------|

Dimensions

| | |
|-----------------------------|----------|
| Depth of installed product | 24 mm |
| Height of installed product | 75 mm |
| Dimensions (LLxwwxhh) | 75x75x36 |
| Width of installed product | 75 mm |

Capacity

| | |
|--------------------------|---|
| Number of modules for WA | 2 |
|--------------------------|---|

Materials

| | |
|------------|-----------------------|
| Colour | white |
| RAL colour | RAL 9010 - Pure white |
| Material | polycarbonate |

Equipment

| | |
|----------------|--|
| Lighting | without lighting (cannot be illuminated) |
| Heating switch | No |

Safety

| | |
|---|------|
| IK protection code against mechanical impacts | 07 |
| Impact strength | IK07 |

Use conditions

| | |
|-------------------------------|-------------|
| Operating temperature | -10...35 °C |
| Storage/transport temperature | -10...50 °C |

Identification

| | |
|-----------------------|-----------------------------|
| Range | essensya |
| Composition | Mechanism with upper casing |
| Appliance switch type | No |

Pictograms

| | |
|------------|------------------|
| Symbole WA | INSTALLATEUR.JPG |
|------------|------------------|
