



WE00150



Pack of 50x 2W Switches Essensya Pure

Technical properties

Architecture

Type of control unit	single rocker
Number of keys	1
Fixing mode	flush-mounting

Controls and indicators

Indicator lamp	no
Push-buttons	No

Main electrical features

Nominal voltage	250 V
Frequency	50/60 Hz

Electric current

Rated current	10 AX
---------------	-------

Dimensions

Depth of installed product	24 mm
Height of installed product	75 mm
Width of installed product	75 mm

Materials

Material	Polycarbonate (PC)
Type of surface treatment	untreated

Installation, mounting

Mounting type	flush-mounted
---------------	---------------

Connection

Type of connection	quick connect
--------------------	---------------

Equipment

Lighting	without lighting (cannot be illuminated)
Heating switch	No

Safety

IK protection code against mechanical impacts	07
Protection index IP	IP21
REACH conform	Yes
RoHS conform	Yes

Halogen free	No
Impact strength	IK07
Use conditions	
Operating temperature	-10...35 °C
Storage/transport temperature	-10...50 °C
Identification	
Appliance switch type	No