



WE00150



## Pack of 50x 2W Switches Essensya Pure

### Technical properties

#### Architecture

Type of control unit	single rocker
Number of keys	1

#### Configuration

Switch mode	Disconnecter
-------------	--------------

#### Controls and indicators

Indicator lamp	no
Push-buttons	No

#### Main electrical features

Nominal voltage	250 V
Frequency	50/60 Hz

#### Electric current

Rated current	10 AX
---------------	-------

#### Dimensions

Depth of installed product	24 mm
Height of installed product	75 mm
Width of installed product	75 mm

#### Materials

Type of surface treatment	untreated
---------------------------	-----------

#### Installation, mounting

Mounting type	flush-mounted
---------------	---------------

#### Connection

Type of connection	quick connect
--------------------	---------------

#### Equipment

Lighting	without lighting (cannot be illuminated)
Heating switch	No

#### Standards

Approvals	EN 60669-1
-----------	------------

#### Safety

IK protection code against mechanical impacts	07
---	----

REACH conform	Yes
RoHS conform	Yes
Halogen free	No
Impact strength	IK07

---

**Use conditions**

Operating temperature	-10...35 °C
Storage/transport temperature	-10...50 °C

---

**Identification**

Composition	Mechanism with upper casing
Appliance switch type	No