



WE00150



## Pack of 50x 2W Switches Essensya Pure

### Technical properties

#### Architecture

Type of control unit	single rocker
Number of keys	1
Fixing mode	flush-mounting

#### Controls and indicators

Indicator lamp	no
Push-buttons	No

#### Main electrical features

Frequency	50/60 Hz
-----------	----------

#### Electric current

Rated current	10 AX
---------------	-------

#### Dimensions

Depth of installed product	24 mm
Height of installed product	75 mm
Width of installed product	75 mm

#### Materials

Type of surface treatment	untreated
---------------------------	-----------

#### Equipment

Lighting	without lighting (cannot be illuminated)
Heating switch	No

#### Safety

IK protection code against mechanical impacts	07
Impact strength	IK07

#### Use conditions

Operating temperature	-10...35 °C
Storage/transport temperature	-10...50 °C

#### Identification

Composition	Mechanism with upper casing
Appliance switch type	No