



WE001G



Essensya 2W switch + claws

Technical properties

Architecture

Type of order	Switch
Type of control unit	single rocker
Number of keys	1

Controls and indicators

Indicator lamp	no
----------------	----

Main electrical features

Nominal voltage	250 V
Frequency	50/60 Hz

Electric current

Rated current	10 AX
---------------	-------

Dimensions

Depth of installed product	35 mm
Height of installed product	70 mm
Dimensions (LLxwxhh)	75x75x36
Width of installed product	75 mm

Capacity

Number of modules for WA	2
--------------------------	---

Materials

Colour	white
RAL colour	RAL 9010 - Pure white
Material	polycarbonate

Installation, mounting

Mounting type	various
---------------	---------

Connection

Connection cross-sect. flexible conductor	1,5 / 2,5mm ²
Connection cross-sect. rigid cable	mini 2x1 mm ² - maxi 2x2,5 mm ²
Connection type	quick connect
Type of contacts	2 way
Type of connection	quick connect

Standards

Approvals	EN 60669-1
-----------	------------

Safety

IK protection code against mechanical impacts

07

Use conditions

Operating temperature

-10...35 °C

Storage/transport temperature

-10...50 °C

Identification

Range

essensya

Composition

Mechanism with upper casing