



WE001G



Essensya 2W switch + claws

Technical properties

Architecture

Type of control unit	single rocker
Number of keys	1
Fixing mode	flush-mounting

Controls and indicators

Indicator lamp	no
----------------	----

Main electrical features

Nominal voltage	250 V
Frequency	50/60 Hz

Electric current

Rated current	10 AX
---------------	-------

Dimensions

Depth of installed product	35 mm
Height of installed product	70 mm
Dimensions (LLxwxhh)	75x75x36
Width of installed product	75 mm

Capacity

Number of modules for WA	2
--------------------------	---

Materials

Colour	white
RAL colour	RAL 9010 - Pure white
Material	Polycarbonate (PC)

Connection

Type of connection	quick connect
--------------------	---------------

Safety

IK protection code against mechanical impacts	07
Protection index IP	IP41

Use conditions

Operating temperature	-10...35 °C
Storage/transport temperature	-10...50 °C