



WE010



Intermediate switch Essensya Pure

Technical properties

Architecture

Type of control unit	single rocker
Number of keys	1
Fixing mode	flush-mounting

Controls and indicators

Indicator lamp	no
Push-buttons	No

Main electrical features

Frequency	50/60 Hz
-----------	----------

Electric current

Rated current	10 AX
---------------	-------

Dimensions

Depth of installed product	24 mm
Height of installed product	75 mm
Dimensions (LLxwwxhh)	75x75x36
Width of installed product	75 mm

Capacity

Number of modules for WA	2
--------------------------	---

Materials

Colour	white
RAL colour	RAL 9010 - Pure white
Material	polycarbonate

Equipment

Lighting	without lighting (cannot be illuminated)
Heating switch	No

Safety

IK protection code against mechanical impacts	07
Impact strength	IK07

Use conditions

Operating temperature	-10...35 °C
Storage/transport temperature	-10...50 °C

Identification

Range	essensya
Composition	Mechanism with upper casing
Appliance switch type	No

Pictograms

Symbole WA	INSTALLATEUR.JPG
------------	------------------
