



WE010



## Intermediate switch Essensya Pure

### Technical properties

#### Architecture

Type of order	Switch
Type of control unit	single rocker
Number of keys	1

#### Configuration

Switch mode	intermediate switch
-------------	---------------------

#### Controls and indicators

Indicator lamp	no
Push-buttons	No

#### Main electrical features

Nominal voltage	250 V
Frequency	50/60 Hz

#### Electric current

Rated current	10 AX
---------------	-------

#### Dimensions

Depth of installed product	24 mm
Height of installed product	75 mm
Dimensions (LLxwxh)	75x75x36
Width of installed product	75 mm

#### Capacity

Number of modules for WA	2
--------------------------	---

#### Materials

Colour	white
RAL colour	RAL 9010 - Pure white
Material	polycarbonate

#### Installation, mounting

Mounting type	various
---------------	---------

#### Connection

Connection cross-sect. flexible conductor	1,5 / 2,5mm <sup>2</sup>
Connection cross-sect. rigid cable	mini 2x1 mm <sup>2</sup> - maxi 2x2,5 mm <sup>2</sup>
Type of contacts	2 way
Type of connection	quick connect

<b>Equipment</b>	
Lighting	without lighting (cannot be illuminated)
Heating switch	No
<b>Standards</b>	
Approvals	EN 60669-1
<b>Safety</b>	
IK protection code against mechanical impacts	07
REACH conform	Yes
RoHS conform	Yes
Halogen free	No
Impact strength	IK07
<b>Use conditions</b>	
Operating temperature	-10...35 °C
Storage/transport temperature	-10...50 °C
<b>Identification</b>	
Range	essensya
Composition	Mechanism with upper casing
Appliance switch type	No
<b>Pictograms</b>	
Symbole WA	INSTALLATEUR.JPG