



WE022



## 2 way push button InterBP + N single Essensya Pure

### Technical properties

#### Architecture

Type of control unit	Push button
Number of keys	1

#### Controls and indicators

Indicator lamp	no
----------------	----

#### Main electrical features

Nominal voltage	250 V
Nominal voltage	250 V
Frequency	50/60 Hz

#### Electric current

Rated current	10 AX
---------------	-------

#### Dimensions

Installation depth, flush-mounted boxes	40 mm
Depth of installed product	24 mm
Height of installed product	75 mm
Width of installed product	70 mm

#### Materials

Colour	white
Material	polycarbonate

#### Installation, mounting

Fixing type	With screws
Mounting type	flush-mounted

#### Connection

Type of contacts	1NC+1NO
Type of connection	quick connect

#### Standards

Approvals	EN 60669-1
-----------	------------

#### Safety

REACH conform	Yes
RoHS conform	Yes
Halogen free	No
Impact strength	IK07

**Use conditions**

---

Operating temperature	-10...35 °C
Storage/transport temperature	-10...50 °C

---

**Identification**

---

Range	essensya
Composition	Mechanism with upper casing

---

**Pictograms**

---

Symbole WA	INSTALLATEUR.JPG
------------	------------------

---