



WE023



## 2 way push button InterBP + N single with Light Essensya Pure

### Technical properties

#### Architecture

Type of control unit	single push button
Number of keys	1
Fixing mode	flush-mounting

#### Main electrical features

Frequency	50/60 Hz
-----------	----------

#### Electric current

Rated current	10 AX
---------------	-------

#### Dimensions

Installation depth, flush-mounted boxes	40 mm
Depth of installed product	24 mm
Height of installed product	75 mm
Dimensions (LLxwwxhh)	75x75x36
Width of installed product	75 mm

#### Capacity

Number of modules for WA	2
--------------------------	---

#### Materials

Colour	white
RAL colour	RAL 9010 - Pure white
Material	polycarbonate

#### Safety

IK protection code against mechanical impacts	07
Impact strength	IK07

#### Use conditions

Operating temperature	-10...35 °C
Storage/transport temperature	-10...50 °C

#### Identification

Range	essensya
Composition	Mechanism with upper casing

#### Pictograms

Symbole WA	INSTALLATEUR.JPG
------------	------------------