



WE023G



Essensya Push button 10+1F with light + claws

Technical properties

Architecture

Type of order	Push button
Type of control unit	Push button
Number of keys	1

Controls and indicators

Indicator lamp	as an accessory
----------------	-----------------

Main electrical features

Nominal voltage	250 V
Frequency	50/60 Hz

Electric current

Rated current	10 A
---------------	------

Dimensions

Depth of installed product	35 mm
Height of installed product	70 mm
Dimensions (LLxwwxhh)	75x75x36
Width of installed product	75 mm

Capacity

Number of modules for WA	2
--------------------------	---

Materials

Colour	white
RAL colour	RAL 9010 - Pure white
Material	polycarbonate

Installation, mounting

Fixing type	With screws or claws
Mounting type	various

Connection

Connection cross-sect. flexible conductor	1,5 / 2,5mm ²
Connection cross-sect. rigid cable	mini 2x1 mm ² - maxi 2x2,5 mm ²
Type of contacts	1NC+1NO
Type of connection	quick connect

Standards

Approvals	EN 60669-1
-----------	------------

Safety

IK protection code against mechanical impacts

07

Use conditions

Operating temperature

-10...35 °C

Storage/transport temperature

-10...50 °C

Identification

Range

essensya

Composition

Mechanism with upper casing