



WE025



2 way push button single InterBP + N with FPL Essensya Pure

Technical properties

Architecture

Type of control unit	single push button
Number of keys	1
Fixing mode	flush-mounting

Main electrical features

Frequency	50/60 Hz
-----------	----------

Electric current

Rated current	10 AX
---------------	-------

Dimensions

Installation depth, flush-mounted boxes	40 mm
Depth of installed product	24 mm
Height of installed product	75 mm
Dimensions (LLxwwxhh)	75x75x36
Width of installed product	75 mm

Capacity

Number of modules for WA	2
--------------------------	---

Materials

Colour	white
RAL colour	RAL 9010 - Pure white
Material	polycarbonate

Safety

IK protection code against mechanical impacts	07
Impact strength	IK07

Use conditions

Operating temperature	-10...35 °C
Storage/transport temperature	-10...50 °C

Identification

Range	essensya
Composition	Mechanism with upper casing

Pictograms

Symbole WA	INSTALLATEUR.JPG
------------	------------------