



WE025G



## Essensya Push button 10+1F with label holder + claws

### Technical properties

#### Architecture

Number of keys	1
Fixing mode	flush-mounting

#### Main electrical features

Frequency	50/60 Hz
-----------	----------

#### Electric current

Rated current	10 A
---------------	------

#### Dimensions

Depth of installed product	35 mm
Height of installed product	70 mm
Dimensions (LLxwxhh)	75x75x36
Width of installed product	75 mm

#### Capacity

Number of modules for WA	2
--------------------------	---

#### Materials

Colour	white
RAL colour	RAL 9010 - Pure white
Material	polycarbonate

#### Safety

IK protection code against mechanical impacts	07
---	----

#### Use conditions

Operating temperature	-10...35 °C
Storage/transport temperature	-10...50 °C

#### Identification

Range	essensya
Composition	Mechanism with upper casing