



WE040



2 way switch double Essensya Pure

Technical properties

Architecture

Type of order	Switch
Type of control unit	double rocker
Number of keys	2

Configuration

Switch mode	Disconnecter
-------------	--------------

Controls and indicators

Indicator lamp	as an accessory
Push-buttons	No

Main electrical features

Nominal voltage	250 V
Frequency	50/60 Hz

Electric current

Rated current	10 AX
---------------	-------

Dimensions

Depth of installed product	24 mm
Height of installed product	75 mm
Dimensions (LLxwwxhh)	75x75x36
Width of installed product	75 mm

Capacity

Number of modules for WA	2
--------------------------	---

Materials

Colour	white
RAL colour	RAL 9010 - Pure white
Material	polycarbonate

Installation, mounting

Mounting type	flush-mounted
---------------	---------------

Connection

Connection cross-sect. flexible conductor	1,5 / 2,5mm ²
Connection cross-sect. rigid cable	mini 2x1 mm ² - maxi 2x2,5 mm ²
Type of contacts	2 way
Type of connection	quick connect

Equipment

Lighting	without lighting (cannot be illuminated)
Heating switch	No

Standards

Approvals	EN 60669-1
-----------	------------

Safety

IK protection code against mechanical impacts	07
REACH conform	Yes
RoHS conform	Yes
Halogen free	No
Impact strength	IK07

Use conditions

Operating temperature	-10...35 °C
Storage/transport temperature	-10...50 °C

Identification

Range	essensya
Composition	Mechanism with upper casing
Appliance switch type	No

Pictograms

Symbole WA	INSTALLATEUR.JPG
------------	------------------