



WE040G



## Essensya 2G2W SW + claws

### Technical properties

#### Architecture

Type of order	Switch
Type of control unit	double rocker
Number of keys	2

#### Controls and indicators

Indicator lamp	as an accessory
----------------	-----------------

#### Main electrical features

Nominal voltage	250 V
Frequency	50/60 Hz

#### Electric current

Rated current	10 AX
---------------	-------

#### Dimensions

Depth of installed product	35 mm
Height of installed product	70 mm
Dimensions (LLxwwxhh)	75x75x36
Width of installed product	75 mm

#### Capacity

Number of modules for WA	2
--------------------------	---

#### Materials

Colour	white
RAL colour	RAL 9010 - Pure white
Material	polycarbonate

#### Installation, mounting

Mounting type	flush-mounted
---------------	---------------

#### Connection

Connection cross-sect. flexible conductor	1,5 / 2,5mm <sup>2</sup>
Connection cross-sect. rigid cable	mini 2x1 mm <sup>2</sup> - maxi 2x2,5 mm <sup>2</sup>
Connection type	quick connect
Type of contacts	2 way
Type of connection	quick connect

#### Standards

Approvals	EN 60669-1
-----------	------------

**Safety**

---

IK protection code against mechanical impacts

07

**Use conditions**

---

Operating temperature

-10...35 °C

Storage/transport temperature

-10...50 °C

**Identification**

---

Range

essensya

Composition

Mechanism with upper casing