



WE044



2 way push button InterBP + N double Essensya Pure

Technical properties

Architecture

Fixing mode flush-mounting

Main electrical features

Frequency 50/60 Hz

Electric current

Rated current 10 AX

Dimensions

Installation depth, flush-mounted boxes 40 mm

Depth of installed product 24 mm

Height of installed product 75 mm

Dimensions (LLxwxhh) 75x75x36

Width of installed product 75 mm

Capacity

Number of modules for WA 2

Materials

Colour white

RAL colour RAL 9010 - Pure white

Material polycarbonate

Safety

IK protection code against mechanical impacts 07

Impact strength IK07

Use conditions

Operating temperature -10...35 °C

Storage/transport temperature -10...50 °C

Identification

Range essensya

Composition Mechanism with upper casing

Pictograms

Symbole WA INSTALLATEUR.JPG