



WE044G



Double push button NO/NC +claws Essensya Pure

Technical properties

Architecture

Type of control unit	double rocker
Number of keys	2

Controls and indicators

Indicator lamp	no
----------------	----

Main electrical features

Nominal voltage	250 V
Nominal voltage	250 V
Frequency	50/60 Hz

Electric current

Rated current	10 AX
---------------	-------

Dimensions

Installation depth, flush-mounted boxes	40 mm
Depth of installed product	24 mm
Height of installed product	75 mm
Width of installed product	75 mm

Materials

Colour	white
Material	polycarbonate
Type of surface treatment	untreated

Installation, mounting

Fixing type	With screws or claws
Mounting type	flush-mounted

Connection

Type of contacts	1NC+1NO
Type of connection	quick connect

Standards

Approvals	EN 60669-1
-----------	------------

Safety

Impact strength	IK07
-----------------	------

Use conditions

Operating temperature	-10...35 °C
Storage/transport temperature	-10...50 °C
Identification	
Range	essensya
Composition	Mechanism with upper casing
Pictograms	
Symbole WA	INSTALLATEUR.JPG