



WE044G



## Double push button NO/NC +claws Essensya Pure

### Technical properties

#### Architecture

Type of control unit	double rocker
Fixing mode	flush-mounting

#### Controls and indicators

Indicator lamp	no
----------------	----

#### Main electrical features

Frequency	50/60 Hz
-----------	----------

#### Electric current

Rated current	10 AX
---------------	-------

#### Dimensions

Installation depth, flush-mounted boxes	40 mm
Depth of installed product	24 mm
Height of installed product	75 mm
Width of installed product	75 mm

#### Materials

Colour	white
Material	polycarbonate
Type of surface treatment	untreated

#### Safety

Impact strength	IK07
-----------------	------

#### Use conditions

Operating temperature	-10...35 °C
Storage/transport temperature	-10...50 °C

#### Identification

Range	essensya
Composition	Mechanism with upper casing

#### Pictograms

Symbole WA	INSTALLATEUR.JPG
------------	------------------