



WE045



2 way push button InterBP double with Light Essensya Pure

Technical properties

Architecture

Type of order	Push button
Type of control unit	double push button
Number of keys	2

Controls and indicators

Indicator lamp	as an accessory
----------------	-----------------

Main electrical features

Nominal voltage	250 V
Nominal voltage	250 V
Frequency	50/60 Hz

Electric current

Rated current	10 AX
---------------	-------

Dimensions

Installation depth, flush-mounted boxes	40 mm
Depth of installed product	24 mm
Height of installed product	75 mm
Dimensions (LLxwwxhh)	75x75x36
Width of installed product	75 mm

Capacity

Number of modules for WA	2
--------------------------	---

Materials

Colour	white
RAL colour	RAL 9010 - Pure white
Material	polycarbonate

Installation, mounting

Fixing type	With screws
Mounting type	flush-mounted

Connection

Connection cross-sect. flexible conductor	1,5 / 2,5mm ²
Connection cross-sect. rigid cable	mini 2x1 mm ² - maxi 2x2,5 mm ²
Type of contacts	1NC+1NO
Type of connection	quick connect

Standards

Approvals

EN 60669-1

Safety

IK protection code against mechanical impacts

07

REACH conform

Yes

RoHS conform

Yes

Halogen free

No

Impact strength

IK07

Use conditions

Operating temperature

-10...35 °C

Storage/transport temperature

-10...50 °C

Identification

Range

essensya

Composition

Mechanism with upper casing

Pictograms

Symbole WA

INSTALLATEUR.JPG