



WE046



## Push button NO/NC + PB NO/NC with light Essensya Pure

### Technical properties

#### Architecture

Fixing mode flush-mounting

#### Main electrical features

Frequency 50/60 Hz

#### Electric current

Rated current 10 AX

#### Dimensions

Installation depth, flush-mounted boxes 40 mm

Depth of installed product 24 mm

Height of installed product 75 mm

Width of installed product 75 mm

#### Capacity

Number of modules for WA 2

#### Materials

Colour white

RAL colour RAL 9010 - Pure white

Material polycarbonate

Type of surface treatment untreated

#### Safety

IK protection code against mechanical impacts 07

Impact strength IK07

#### Use conditions

Operating temperature -10...35 °C

Storage/transport temperature -10...50 °C

#### Identification

Range essensya

Composition Mechanism with upper casing