



WE046



Push button NO/NC + PB NO/NC with light Essensya Pure

Technical properties

Architecture

Type of order	Push button
Type of control unit	double push button
Number of keys	2

Controls and indicators

Indicator lamp	as an accessory
----------------	-----------------

Main electrical features

Nominal voltage	250 V
Frequency	50/60 Hz

Electric current

Rated current	10 AX
---------------	-------

Dimensions

Installation depth, flush-mounted boxes	40 mm
Depth of installed product	24 mm
Height of installed product	75 mm
Width of installed product	75 mm

Capacity

Number of modules for WA	2
--------------------------	---

Materials

Colour	white
RAL colour	RAL 9010 - Pure white
Material	polycarbonate
Type of surface treatment	untreated

Installation, mounting

Fixing type	With screws
Mounting type	flush-mounted

Connection

Connection cross-sect. flexible conductor	1,5 / 2,5mm ²
Connection cross-sect. rigid cable	mini 2x1 mm ² - maxi 2x2,5 mm ²
Type of contacts	1NC+1NO
Type of connection	quick connect

Standards

Safety

IK protection code against mechanical impacts	07
---	----

Impact strength	IK07
-----------------	------

Use conditions

Operating temperature	-10...35 °C
-----------------------	-------------

Storage/transport temperature	-10...50 °C
-------------------------------	-------------

Identification

Range	essensya
-------	----------

Composition	Mechanism with upper casing
-------------	-----------------------------