



WE046T

Push button NO/NC + PB NO/NC with light Essensya Titane

Technical properties

Architecture

Fixing mode	flush-mounting
-------------	----------------

Main electrical features

Frequency	50/60 Hz
-----------	----------

Electric current

Rated current	10 AX
---------------	-------

Dimensions

Installation depth, flush-mounted boxes	40 mm
Depth of installed product	24 mm
Height of installed product	75 mm
Width of installed product	75 mm

Capacity

Number of modules for WA	2
--------------------------	---

Materials

RAL colour	RAL 9006 - White aluminium
Material	polycarbonate

Safety

Impact strength	IK07
-----------------	------

Use conditions

Operating temperature	-10...35 °C
Storage/transport temperature	-10...50 °C

Identification

Range	essensya
Composition	Mechanism with upper casing