



WE046T

## Push button NO/NC + PB NO/NC with light Essensya Titane

### Technical properties

#### Architecture

Type of order	Push button
Type of control unit	double push button
Number of keys	2

#### Controls and indicators

Indicator lamp	as an accessory
----------------	-----------------

#### Main electrical features

Nominal voltage	250 V
Frequency	50/60 Hz

#### Electric current

Rated current	10 AX
---------------	-------

#### Dimensions

Installation depth, flush-mounted boxes	40 mm
Depth of installed product	24 mm
Height of installed product	75 mm
Width of installed product	75 mm

#### Capacity

Number of modules for WA	2
--------------------------	---

#### Materials

Material	polycarbonate
----------	---------------

#### Installation, mounting

Fixing type	With screws
Mounting type	flush-mounted

#### Connection

Connection cross-sect. flexible conductor	1,5 / 2,5mm <sup>2</sup>
Connection cross-sect. rigid cable	mini 2x1 mm <sup>2</sup> - maxi 2x2,5 mm <sup>2</sup>
Type of contacts	1NC+1NO
Type of connection	quick connect

#### Standards

Approvals	EN 60669-1
-----------	------------

#### Safety

**Use conditions**

---

Operating temperature	-10...35 °C
-----------------------	-------------

---

Storage/transport temperature	-10...50 °C
-------------------------------	-------------

**Identification**

---

Range	essensya
-------	----------

---

Composition	Mechanism with upper casing
-------------	-----------------------------