



WE049



Push button for ventilation Essensya Pure

Technical properties

Architecture

Type of control unit	single rocker
Number of keys	1
Fixing mode	flush-mounting

Controls and indicators

Indicator lamp	no
Number of buttons	1

Main electrical features

Frequency	50/60 Hz
-----------	----------

Electric current

Rated current	10 AX
---------------	-------

Dimensions

Insertion depth	37 mm
Installation depth, flush-mounted boxes	40 mm
Depth of installed product	24 mm
Height of installed product	75 mm
Width of installed product	75 mm

Materials

Colour	white
RAL colour	RAL 9016 - Traffic white
Material	Polycarbonate (PC)
Type of surface treatment	untreated

Installation, mounting

Fixing type	With screws
-------------	-------------

Equipment

Lighting	without lighting (cannot be illuminated)
Heating switch	No

Safety

Protection index IP	IP20
REACH conform	Yes
RoHS conform	Yes
Halogen free	No
Impact strength	IK07

Use conditions

Operating temperature -10...35 °C

Storage/transport temperature -10...50 °C

Pictograms

Symbole WA

INSTALLATEUR.JPG