



WE049



Push button for ventilation Essensya Pure

Technical properties

Architecture

Type of control unit	single rocker
Number of keys	1

Configuration

Switch mode	2 way
-------------	-------

Controls and indicators

Indicator lamp	no
Number of buttons	1
Push-buttons	Yes

Main electrical features

Nominal voltage	250 V
Nominal voltage	250 V
Frequency	50/60 Hz

Electric current

Rated current	10 AX
---------------	-------

Dimensions

Insertion depth	37 mm
Installation depth, flush-mounted boxes	40 mm
Depth of installed product	24 mm
Height of installed product	75 mm
Width of installed product	75 mm

Materials

Colour	white
Type of surface treatment	untreated

Installation, mounting

Fixing type	With screws
Mounting type	flush-mounted

Connection

Type of contacts	2 way
Type of connection	quick connect

Equipment

Lighting	without lighting (cannot be illuminated)
----------	--

Standards

Approvals	EN 60669-1
-----------	------------

Safety

REACH conform	Yes
---------------	-----

RoHS conform	Yes
--------------	-----

Halogen free	No
--------------	----

Impact strength	IK07
-----------------	------

Use conditions

Operating temperature	-10...35 °C
-----------------------	-------------

Storage/transport temperature	-10...50 °C
-------------------------------	-------------

Identification

Range	essensya
-------	----------

Composition	Mechanism with upper casing
-------------	-----------------------------

Pictograms

Symbole WA	INSTALLATEUR.JPG
------------	------------------