



WE050

Essensya PIR without neutral 2 wires

Technical properties

Architecture

Fixing mode flush-mounting

Functions

Remote operation No

With switch function No

Main electrical features

Frequency 50/60 Hz

Dimensions

Height of installed product 45 mm

Width of installed product 45 mm

Power

Maximum power per output for incandescent bulbs 60 / 320 W

Capacity

Number of modules for WA 2

Detection

Detection angle 180 °

Sensor type detector of movement

Frontal detecting distance 10 m

Side detecting distance 5 m

Materials

Colour white

Colour white

RAL colour RAL 9010 - Pure white

Material polycarbonate

Lighting control

Photocell sensitivity 5 / 800 Lux

Installation, mounting

Maximum Mounting Height 1.2 m

Settings

Comfort temperature setpoint 5 / 40 °C

Delay ON 2 s

Delay OFF

30 mn

Safety

IK protection code against mechanical impacts

07

Protection index IP

IP20

Identification

Range

essensya