



WE050

Essensya PIR without neutral 2 wires

Technical properties

Functions

Remote operation	No
With switch function	No

Main electrical features

Nominal voltage	230 V
Frequency	50/60 Hz

Dimensions

Height of installed product	45 mm
Width of installed product	45 mm

Power

Maximum power per output for incandescent bulbs	60 / 320 W
---	------------

Capacity

Number of modules for WA	2
--------------------------	---

Detection

Detection angle	180 °
Sensor type	detector of movement
Frontal detecting distance	10 m
Side detecting distance	5 m

Materials

Colour	white
Colour	white
RAL colour	RAL 9010 - Pure white
Material	polycarbonate
Surface appearance	glossy

Lighting control

Photocell sensitivity	5 / 800 Lux
-----------------------	-------------

Installation, mounting

Maximum Mounting Height	1.2 m
-------------------------	-------

Connection

Type of connection	with screw
--------------------	------------

Settings

Comfort temperature setpoint	5 / 40 °C
Delay ON	2 s
Time delayed range	2s à 30 min
Delay OFF	30 mn
Safety	
IK protection code against mechanical impacts	07
Identification	
Range	essensya