



WE051

Essensya PIR 3 wires

Technical properties

Architecture

Fixing mode	flush-mounting
-------------	----------------

Functions

Remote operation	No
With switch function	No

Main electrical features

Frequency	50/60 Hz
-----------	----------

Dimensions

Height of installed product	45 mm
Width of installed product	45 mm

Capacity

Number of modules for WA	2
--------------------------	---

Detection

Detection angle	180 °
Sensor type	detector of movement
Frontal detecting distance	10 m
Side detecting distance	5 m

Materials

Colour	white
Colour	white
RAL colour	RAL 9010 - Pure white
Material	polycarbonate
Type of surface treatment	Painted

Lighting control

Photocell sensitivity	5 / 800 Lux
-----------------------	-------------

Installation, mounting

Maximum Mounting Height	1.2 m
-------------------------	-------

Settings

Comfort temperature setpoint	5 / 40 °C
Delay ON	2 s
Delay OFF	30 mn

Safety

IK protection code against mechanical impacts

07

Protection index IP

IP20

Identification

Range

essensya