



WE052T



Automatic switch Essensya 2 wires without neut Titane

Technical properties

Functions

Remote operation	No
With switch function	No

Main electrical features

Frequency	50/60 Hz
-----------	----------

Detection

Detection angle	180 °
Sensor type	detector of movement
Frontal detecting distance	12 m
Side detecting distance	8 m

Materials

Material	plastic
Surface appearance	matt
Type of surface treatment	untreated

Lighting control

Photocell sensitivity	5 / 1000 Lux
-----------------------	--------------

Connection

Type of connection	Screwed terminal
--------------------	------------------

Settings

Delay ON	0 s
Delay OFF	0 s

Safety

IK protection code against mechanical impacts	IK03
---	------

Use conditions

Operating temperature	-5...45 °C
-----------------------	------------