



WE053



Automatic switch Essensya 3 wires Pure White

Technical properties

Architecture

Fixing mode flush-mounting

Functions

Remote operation No

With switch function No

Main electrical features

Frequency 50/60 Hz

Detection

Detection angle 180 °

Sensor type detector of movement

Frontal detecting distance 12 m

Side detecting distance 8 m

Materials

Colour white

Material plastic

Type of surface treatment untreated

Lighting control

Photocell sensitivity 5 / 1000 Lux

Settings

Delay ON 0 s

Delay OFF 0 s

Safety

Protection index IP IP20

Use conditions

Operating temperature -5...45 °C