



WE054T



Automatic switch Essensya slave and staircase Titane

Technical properties

Architecture

Fixing mode	flush-mounting
-------------	----------------

Functions

Remote operation	No
With switch function	No

Main electrical features

Frequency	50/60 Hz
-----------	----------

Detection

Detection angle	180 °
Sensor type	detector of movement
Frontal detecting distance	12 m
Side detecting distance	8 m

Materials

RAL colour	RAL 9006 - White aluminium
Material	plastic
Surface appearance	matt
Type of surface treatment	untreated

Lighting control

Photocell sensitivity	5 / 1000 Lux
-----------------------	--------------

Settings

Delay ON	0 s
Delay OFF	0 s

Safety

Protection index IP	IP20
---------------------	------

Use conditions

Operating temperature	-5...45 °C
-----------------------	------------