



WE063

Essensya Rotative dimmer 400VA ferro transformer

Technical properties

Architecture

Fixing mode	flush-mounting
-------------	----------------

Main electrical features

Frequency	50/60 Hz
-----------	----------

Dimensions

Depth of installed product	48 mm
Height of installed product	70 mm
Width of installed product	70 mm

Capacity

Number of modules for WA	2
--------------------------	---

Materials

Colour	white
RAL colour	RAL 9010 - Pure white
Material	Polycarbonate (PC)
Type of surface treatment	Painted

Installation, mounting

Fixing type	With screws
Mounting type	flush-mounted

Connection

Type of connection	with screw
--------------------	------------

Equipment

Type of dimmer	Yes
Bidirectional radio frequency	Yes

Safety

IK protection code against mechanical impacts	07
Protection index IP	IP20