



WE063

Essensya Rotative dimmer 400VA ferro transformer

Technical properties

Architecture

Type	Halogen
Fixing mode	flush-mounting

Main electrical features

Frequency	50/60 Hz
-----------	----------

Dimensions

Depth of installed product	48 mm
Height of installed product	70 mm
Width of installed product	70 mm

Capacity

Number of modules for WA	2
--------------------------	---

Materials

Colour	white
RAL colour	RAL 9010 - Pure white
Material	polycarbonate
Type of surface treatment	Painted

Equipment

Type of dimmer	Yes
Bidirectional radio frequency	Yes

Safety

IK protection code against mechanical impacts	07
Protection index IP	IP20

Identification

Range	essensya
Composition	Mechanism with upper casing