



WE063

Essensya Rotative dimmer 400VA ferro transformer

Technical properties

Architecture

Type of order	Dimmer
Type	Halogen

Main electrical features

Frequency	50/60 Hz
-----------	----------

Dimensions

Depth of installed product	48 mm
Height of installed product	70 mm
Width of installed product	70 mm

Capacity

Number of modules for WA	2
--------------------------	---

Materials

Colour	white
RAL colour	RAL 9010 - Pure white
Material	polycarbonate
Surface appearance	glossy

Installation, mounting

Fixing type	With screws
Mounting type	flush-mounted

Connection

Connection cross-sect. flexible conductor	1,5 / 2,5mm ²
Connection cross-sect. rigid cable	mini 2x1 mm ² - maxi 2x2,5 mm ²
Type of connection	with screw

Equipment

Type of dimmer	Yes
Bidirectional radio frequency	Yes

Safety

IK protection code against mechanical impacts	07
---	----

Identification

Range	essensya
Composition	Mechanism with upper casing