



WE10050



Essensya Pack of 50x sockets 2P+E 16A 250V screwless

Technical properties

Architecture

Type of pole 2P+T

Configuration

Number of modules 2

Controls and indicators

With or without indicator without

Dimensions

Depth 37 mm

Dimensions (LLxwwxhh) 75x75x37

Capacity

Number of modules for WA 2

Materials

Surface appearance glossy

Installation, mounting

Mounting type flush mounted / surface mounted

Connection

Connection cross-sect. rigid cable 1,5 / 2,5mm²

Phase pickup L1

Standards

Approvals NF

Safety

Protection without protective screen

Identification

Range essensya