



WE100G



## Essensya Socket 2P+T 16A 250V screwless + claws

### Technical properties

#### Architecture

Type of pole 2P+T

#### Configuration

Number of modules 2

#### Controls and indicators

With or without indicator without

#### Dimensions

Depth 37 mm

Dimensions (LLxwwxhh) 75x75x37

#### Capacity

Number of modules for WA 2

#### Materials

Surface appearance glossy

#### Installation, mounting

Mounting type flush mounted / surface mounted

#### Connection

Connection cross-sect. rigid cable 1,5 / 2,5mm<sup>2</sup>

Phase pickup L1

#### Standards

Approvals NF

#### Safety

Protection without protective screen

#### Identification

Range essensya