



WE123



## Socket 2P+T 16A 250V screwless triple Pure

### Technical properties

#### Configuration

Number of modules	2
-------------------	---

#### Controls and indicators

With or without indicator	without
---------------------------	---------

#### Main electrical features

Nominal voltage	250 V
-----------------	-------

#### Dimensions

Depth	37 mm
-------	-------

Dimensions (LLxwwxhh)	217x70.5x30
-----------------------	-------------

#### Capacity

Number of modules for WA	2
--------------------------	---

#### Materials

Surface appearance	glossy
--------------------	--------

Surface protection	Brilliant
--------------------	-----------

#### Installation, mounting

Mounting type	flush mounted / surface mounted
---------------	---------------------------------

#### Connection

Connection cross-sect. rigid cable	1,5 / 2,5mm <sup>2</sup>
------------------------------------	--------------------------

Phase pickup	L1
--------------	----

#### Standards

Approvals	NFC 61314
-----------	-----------

#### Safety

REACH conform	Yes
---------------	-----

RoHS conform	Yes
--------------	-----

Halogen free	No
--------------	----

Protection	without protective screen
------------	---------------------------

#### Identification

Range	essensya
-------	----------