



WE155

## Monobloc cable outlet Essensya Pure

### Technical properties

#### Architecture

Fixing mode	flush-mounting
-------------	----------------

#### Functions

Integrated earth fault protection	No
Centralized terminal connections	No
With orientation lighting	No
Overvoltage protection	No

#### Configuration

Number of modules	2
-------------------	---

#### Compatibility

IFTTT support available	No
-------------------------	----

#### Controls and indicators

Indicator lamp	no
----------------	----

#### Connectivity

With USB charging socket	No
--------------------------	----

#### Main electrical features

Frequency	50/60 Hz
-----------	----------

#### Electric current

Rated current	16 A
---------------	------

#### Dimensions

Depth	37 mm
Installation depth, flush-mounted boxes	40 mm
Depth of installed product	22.8 mm
Height of installed product	80 mm
Width of installed product	70 mm

#### Capacity

Number of module locations	0
----------------------------	---

#### Cover, door

Interlockable	No
---------------	----

#### Power supply

Special power supply	Other
----------------------	-------

**Materials**

Colour	white
Type of surface treatment	untreated
Transparent	No
Metallic colour	No

**Connection**

Number of accessible phases	0
-----------------------------	---

**Accessories included**

With miniature fuse	No
---------------------	----

**Equipment**

Number of units	1
Number of socket outlets switchable	0
On/Off switch	No
With transparent product label holder	No

**Safety**

Protection index IP	IP20
---------------------	------

**Use conditions**

Insulated	Yes
-----------	-----

**Identification**

Range	essensya
Version	Other