



WE155

Monobloc cable outlet Essensya Pure

Technical properties

Architecture

Fixing mode	flush-mounting
-------------	----------------

Functions

Integrated earth fault protection	No
Centralized terminal connections	No
With orientation lighting	No
Overvoltage protection	No

Configuration

Number of modules	2
-------------------	---

Compatibility

IFTTT support available	No
-------------------------	----

Controls and indicators

Indicator lamp	no
----------------	----

Connectivity

With USB charging socket	No
--------------------------	----

Main electrical features

Nominal voltage	250 V
Frequency	50/60 Hz

Electric current

Rated current	16 A
---------------	------

Dimensions

Depth	37 mm
Installation depth, flush-mounted boxes	40 mm
Depth of installed product	22.8 mm
Height of installed product	80 mm
Width of installed product	70 mm

Capacity

Number of module locations	0
----------------------------	---

Cover, door

Interlockable	No
---------------	----

Power supply

Special power supply	Other
----------------------	-------

Materials

Colour	white
Material	Polycarbonate (PC)
Type of surface treatment	untreated
Transparent	No
Metallic colour	No

Installation, mounting

Fixing type	With screws
-------------	-------------

Connection

Number of accessible phases	0
Type of connection	Screw/Bride

Accessories included

With miniature fuse	No
---------------------	----

Equipment

Number of units	1
Number of socket outlets switchable	0
On/Off switch	No
With transparent product label holder	No

Standards

Approvals	NFC 61314
-----------	-----------

Safety

IK protection code against mechanical impacts	IK05
Protection index IP	IP20
REACH conform	Yes
RoHS conform	Yes
Halogen free	Yes

Use conditions

Insulated	Yes
-----------	-----

Identification

Version	Other
---------	-------