



WE156

Cable outlet Essensya Pure

Technical properties

Architecture

Fixing mode	flush-mounting
-------------	----------------

Functions

Integrated earth fault protection	No
Centralized terminal connections	No
With orientation lighting	No
Overvoltage protection	No

Configuration

Number of modules	2
-------------------	---

Compatibility

IFTTT support available	No
-------------------------	----

Controls and indicators

Indicator lamp	no
----------------	----

Connectivity

With USB charging socket	No
--------------------------	----

Main electrical features

Frequency	50/60 Hz
-----------	----------

Electric current

Rated current	16 A
---------------	------

Dimensions

Depth	37 mm
Installation depth, flush-mounted boxes	40 mm
Depth of installed product	22.8 mm
Height of installed product	75 mm
Width of installed product	75 mm

Capacity

Number of module locations	0
----------------------------	---

Cover, door

Interlockable	No
---------------	----

Power supply

Special power supply	Other
----------------------	-------

Materials

Colour	white
Type of surface treatment	untreated
Transparent	No
Metallic colour	No

Connection

Number of accessible phases	0
-----------------------------	---

Accessories included

With miniature fuse	No
---------------------	----

Equipment

Number of units	1
Number of socket outlets switchable	0
On/Off switch	No
With transparent product label holder	No

Safety

Protection index IP	IP20
---------------------	------

Use conditions

Insulated	Yes
-----------	-----

Identification

Range	essensya
Version	Other