



WE200

## French telephone socket T Essensya Pure

### Technical properties

#### Architecture

Type	T
Fixing mode	flush-mounting

#### Configuration

Antibacterial treatment	No
-------------------------	----

#### Connectivity

Direction of outlet (for data sockets copper)	straight
---	----------

#### Dimensions

Installation depth, flush-mounted boxes	40 mm
Depth of installed product	15 mm
Height of installed product	75 mm
Length	45 mm
Dimensions (LLxwwxhh)	75x75x28
Width of installed product	75 mm

#### Capacity

Number of modules for WA	2
Number of module locations	2

#### Materials

Colour	white
RAL colour	RAL 9010 - Pure white

#### Equipment

Number of outputs	1
With transparent product label holder	No

#### Safety

Protection index IP	IP20
Glow wire test	according to CEI 695-2-1: 650°C

#### Identification

Range	essensya
Composition	Mechanism with upper casing
With imprint	No