



WE200

French telephone socket T Essensya Pure

Technical properties

Architecture

Type	T
------	---

Configuration

Antibacterial treatment	No
-------------------------	----

Connectivity

Direction of outlet (for data sockets copper)	straight
---	----------

Dimensions

Installation depth, flush-mounted boxes	40 mm
Depth of installed product	15 mm
Height of installed product	75 mm
Length	45 mm
Dimensions (LLxwwxhh)	75x75x28
Width of installed product	75 mm

Capacity

Number of modules for WA	2
Number of module locations	2

Materials

Colour	white
RAL colour	RAL 9010 - Pure white
Surface appearance	glossy
Surface protection	Brilliant

Installation, mounting

Fixing type	With screws
Mounting type	various

Connection

Type of connection	with screw
--------------------	------------

Equipment

Number of outputs	1
With transparent product label holder	No

Safety

IK protection code against mechanical impacts	01
---	----

Glow wire test	according to CEI 695-2-1: 650°C
REACH conform	Yes
RoHS conform	Yes
Halogen free	No
Identification	
Category	Other
Range	essensya
Composition	Mechanism with upper casing
With imprint	No