



WE223G

Essensya RJ45 Cat.6 FTP + claws

Technical properties

Architecture

Type	FTP
Fixing mode	flush-mounting

Dimensions

Depth of installed product	11 mm
Height of installed product	70 mm
Dimensions (LLxwwxhh)	75x75x35
Width of installed product	75 mm

Capacity

Number of modules for WA	2
Number of module locations	2

Materials

Colour	white
RAL colour	RAL 9010 - Pure white
Material	polycarbonate
Material	Polycarbonate (PC)
Surface appearance	glossy
Surface protection	Brilliant
Type of surface treatment	Painted

Installation, mounting

Fixing type	With screws or claws
Mounting type	various

Connection

Type of connection	quick connect
--------------------	---------------

Equipment

With transparent product label holder	Yes
---------------------------------------	-----

Safety

IK protection code against mechanical impacts	01
Protection index IP	IP20
Glow wire test	according to CEI 695-2-1: 650°C

Identification

Category	Cat6
----------	------

