



WE223G

## Essensya RJ45 Cat.6 FTP + claws

### Technical properties

#### Architecture

Type	FTP
------	-----

#### Dimensions

Depth of installed product	11 mm
Height of installed product	70 mm
Dimensions (LLxwwxhh)	75x75x35
Width of installed product	75 mm

#### Capacity

Number of modules for WA	2
Number of module locations	2

#### Materials

Colour	white
RAL colour	RAL 9010 - Pure white
Material	polycarbonate
Surface appearance	glossy
Surface protection	Brilliant

#### Installation, mounting

Fixing type	With screws or claws
Mounting type	various

#### Connection

Type of connection	quick connect
--------------------	---------------

#### Equipment

With transparent product label holder	Yes
---------------------------------------	-----

#### Safety

IK protection code against mechanical impacts	01
Glow wire test	according to CEI 695-2-1: 650°C

#### Identification

Category	Cat6
Range	essensya
Composition	Mechanism with upper casing