



WE226

RJ45 CAT.6 STP single Essensya Pure

Technical properties

Architecture

Type	STP
Fixing mode	flush-mounting

Configuration

Antibacterial treatment	No
-------------------------	----

Connectivity

Direction of outlet (for data sockets copper)	straight
---	----------

Dimensions

Installation depth, flush-mounted boxes	40 mm
Depth of installed product	11 mm
Height of installed product	75 mm
Dimensions (LLxwxh)	75x75x35
Width of installed product	75 mm

Capacity

Number of modules for WA	2
Number of module locations	2

Materials

Colour	white
RAL colour	RAL 9010 - Pure white
Material	polycarbonate
Material	Polycarbonate (PC)
Surface appearance	glossy
Type of surface treatment	shiny

Installation, mounting

Fixing type	With screws
Mounting type	various

Connection

Type of connection	quick connect
--------------------	---------------

Equipment

Number of outputs	1
With transparent product label holder	Yes

Safety

IK protection code against mechanical impacts	01
Protection index IP	IP20
Glow wire test	according to CEI 695-2-1: 650°C

Identification

Category	Cat6
Range	essensya
Composition	Mechanism with upper casing
With imprint	No