



WE226

RJ45 CAT.6 STP single Essensya Pure

Technical properties

Architecture

Type	STP
------	-----

Configuration

Antibacterial treatment	No
-------------------------	----

Connectivity

Direction of outlet (for data sockets copper)	straight
---	----------

Dimensions

Installation depth, flush-mounted boxes	40 mm
---	-------

Depth of installed product	11 mm
----------------------------	-------

Height of installed product	75 mm
-----------------------------	-------

Dimensions (LLxwwxhh)	75x75x35
-----------------------	----------

Width of installed product	75 mm
----------------------------	-------

Capacity

Number of modules for WA	2
--------------------------	---

Number of module locations	2
----------------------------	---

Materials

Colour	white
--------	-------

RAL colour	RAL 9010 - Pure white
------------	-----------------------

Material	polycarbonate
----------	---------------

Surface appearance	glossy
--------------------	--------

Installation, mounting

Fixing type	With screws
-------------	-------------

Mounting type	various
---------------	---------

Connection

Type of connection	quick connect
--------------------	---------------

Equipment

Number of outputs	1
-------------------	---

With transparent product label holder	Yes
---------------------------------------	-----

Safety

IK protection code against mechanical impacts	01
---	----

Glow wire test	according to CEI 695-2-1: 650°C
----------------	---------------------------------

REACH conform	Yes
RoHS conform	Yes
Halogen free	No

Identification

Category	Cat6
Range	essensya
Composition	Mechanism with upper casing
With imprint	No