



WE253G



essensya TV+FM direct socket + claws

Technical properties

Architecture

Type TV+FM

Connectivity

Passband 4 - 862 MHz

Dimensions

Depth of installed product 11 mm

Height of installed product 75 mm

Dimensions (LLxwxhh) 75x75x32

Width of installed product 75 mm

Attenuation

Tap loss at 860 MHz 1 dB

Capacity

Number of modules for WA 2

Materials

Colour white

RAL colour RAL 9010 - Pure white

Installation, mounting

Mounting type various

Connection

Type of connection with screw

Equipment

Number of outputs 2

Safety

IK protection code against mechanical impacts 01

Glow wire test according to CEI 695-2-1: 650°C

Identification

Range essensya