



WE253T

## TV+FM twin direct Essensya Titane

### Technical properties

#### Architecture

Type	TV+FM
Fixing mode	flush-mounting

#### Configuration

Antibacterial treatment	No
-------------------------	----

#### Connectivity

Passband	4 - 862 MHz
----------	-------------

#### Dimensions

Depth of installed product	11 mm
Height of installed product	75 mm
Dimensions (LLxwwxhh)	75x75x32
Width of installed product	75 mm

#### Attenuation

Tap loss at 860 MHz	1 dB
---------------------	------

#### Capacity

Number of modules for WA	2
--------------------------	---

#### Materials

Colour	white
RAL colour	RAL 9006 - White aluminium

#### Equipment

Number of outputs	2
-------------------	---

#### Safety

Protection index IP	IP20
Glow wire test	according to CEI 695-2-1: 650°C

#### Identification

Range	essensya
-------	----------